

PRESCRIPTION ORDER FORM



Tel (800) 780-4292 Fax (425) 486-3553
Tel (425) 486-4292 PacificOrthotic.com

\$30 Rush Order - Due By Date: /

New Casting Prior Casting On File

# of Same Pairs: 1 2 3

LAB USE ONLY

LAB USE ONLY

Provider Facility Account # City State Zip Telephone Email

Patient Date PO Date of Birth Age Weight Shoe M W K Size Style

Select designed devices (descriptions on back)

Order Specialty Device

- Sport: Aerobic, Super Sport, Poly Athletic, Carbo Athletic, Ski Orthotic, Dress: Carbo Dress
Comfort: Soft Step, Cork & Leather, Poly Accommodative, AliPlast Accommodative, Foot Forms: Cork (55 Durometer), Blue (45 Durometer)
Diabetic: Poly Hybrid Diabetic, White EVA DMII Insole, Cork EVA DMII Insole
Special Control: Whitman Roberts, In-toeing Gait Plate, Out-toeing Gait Plate

Order By Diagnoses

- Achilles Tendinitis, Adult Acquired Flatfoot/PTTD, Calcaneal Apophysitis, Hallux Limitus/HAV, In-toeing Gait, Lateral Ankle Instability, Lateral Column Overload, Metatarsalgia, Neuroma, Pediatric Flatfoot, Pes Cavus with Rigid Forefoot, Plantar Fasciitis Due to Everted Rear Foot, Plantar Fasciitis Due to Forefoot Valgus, Sesamoiditis, Sinus Tarsi Syndrome, Tarsal Tunnel Syndrome

Further customize designed devices or order separately below

Heel Bisection

- Perpendicular, As-Is, Invert: R L, Evert: R L

Heel Cup

- Shallow (10mm), Normal (14mm), Deep (18mm), Custom

Shell Width

- Narrow, Normal, Wide

Cast Fill

- Heavy (Minimal Arch), Normal, Light (Maximal Arch)

Cast Work

- Medial Flange (Wide Shell Only), Lateral Clip, Medial Heel Skive: R mm L mm, Lateral Heel Skive: R mm L mm

Polymer Shell

Polypropylene:

- 3/32" (2.3mm), 1/8" (3.2mm), 5/32" (4.0mm), 3/16" (4.7mm), 1/4" (6.4mm)

Table with 6 columns: Weight (≤ 100lb, 101-160lb, 161-220lb, 221-280lb, ≥ 281) and 6 rows of shell thicknesses (2.3mm to 6.4mm) with material descriptions like Semi-Rigid, Rigid, Very Rigid, Flexible.

Graphite Shell

XTXS Carboplast II:

- 1.6mm "Ease-Flex", 2.0mm "Semi-Rigid", 2.6mm "Rigid", 3.0mm "Ultra-Rigid"

Table with 4 columns: Weight (≤ 100lb, 101-180lb, ≥ 181lb) and 4 rows of shell thicknesses (1.6mm to 3.0mm) with material descriptions like Semi-Rigid, Rigid, Very Rigid, Flexible.

NW DBX6: 1.5mm #4 Flex (Rigid)

Arch Fill

- FULL -or- Lateral Only, PPT (poron), Multicork, EVA (Soft), EVA (Medium), EVA (Firm)

Forefoot Posting

- Intrinsic, Extrinsic, Right: Varus Valgus, Left: Varus Valgus

Rear Foot Posting (Extrinsic)

- None (spot grind), Standard w/ No Cap, Petite/Strip Post, Material: Polypropylene (Polymer Shell Only), Birko Cork, Crepe Firm (60 Durometer), Crepe Extra-Firm (70+ Durometer)

- Angle: 0°/0° neutral 4°/4° motion, Right: Varus Valgus, Left: Varus Valgus


- Other: Heel Lift: R mm L mm, No Lateral Bevel, Lateral Post Flare

Shell Modifications

- Rigid Morton's 1st Toe Extension, 1st Ray Cut Out, Plantar Fascial Groove mm, Heel Hole w/ Poron Backfill

Additions

- Metatarsal Pad mm, Metatarsal Raise mm, Metatarsal Bar mm, Scaphoid/Arch Pad mm, Soft Medial Overlay, Morton's Extension (Flexible), Reverse Morton's Extension (Flexible), Horseshoe Heel Spur Pad, Heel Cushion, Silicone Gel Pad (diagram location)



\*Mark Additional Accommodations on Diagram and Casting\*

Forefoot Extension

- Sulcus 1/4 Length, Full Length, 1/16", 1/8", PPT (Poron), HR EVA, Multicork

Cushion Layer

- Met Length, Sulcus 1/4 Length, Full Length, 1/16", 1/8", PPT (Poron), HR EVA, Plastazote

Top Cover

- No Top Cover -or- Black, Tan, Vinyl, Leather, Ultrasuede

-Or-

- Met Length, Sulcus 1/4 Length, Full Length, 1/16", 1/8", Spenco, Puff EVA, Perforated Puff, X-Static, Plastazote

Bottom Cover

- Vinyl, Ultrasuede, Puff EVA, Multicork

Diagnosis / Special Instructions

**Order Specialty Device**

**Order By Diagnoses**

<p><b>Aerobic</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 1/8" Polypropylene  <b>Rearfoot Posting:</b> Crepe Firm @ 0°/0° w/ No Cap  <b>Additional:</b> EVA (Medium) Arch Fill  <b>Covers:</b> Full Length 1/8" Neoprene Top, Puff EVA Bottom</p>	<p><b>Super Sport</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 1/8" Polypropylene  <b>Rearfoot Posting:</b> Crepe Firm @ 0°/0° w/ No Cap  <b>Additional:</b> EVA (Medium) Arch Fill  <b>Covers:</b> Full Length 1/8" Poron Cushion, Black Vinyl Top, Puff EVA Bottom</p>	<p><b>Achilles Tendinitis</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal + 3° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0° No Lateral Bevel  <b>Additional:</b> 3mm Heel Lift  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Adult Acquired Flatfoot (also, PTTD)</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep + 3° Medial Heel Skive  <b>Shell Width:</b> Wide + Medial Flange  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> None  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Poly Athletic</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> None  <b>Covers:</b> Full Length 1/8" Puff EVA Top, Ultrasuede Bottom</p>	<p><b>Carbo Athletic</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> Carboplast II Semi-Rigid by Weight  <b>Rearfoot Posting:</b> Crepe Firm @ 0°/0°  <b>Additional:</b> None  <b>Covers:</b> Full Length "6/6" Blue BiLam (PPT + Blue EVA) Top, Ultrasuede Bottom</p>	<p><b>Calcaneal Apophysitis</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep + 3° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> 3mm Heel Lift, Heel Cushion  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Hallux Limitus (also, HAV)</b>  <b>Heel Bisection:</b> Inverted 3°  <b>Heel Cup:</b> Normal + 3° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> Reverse Morton's Extension  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Ski Orthotic</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Shallow  <b>Shell Width:</b> Narrow  <b>Cast Fill:</b> Normal  <b>Shell:</b> NW DBX6 Rigid  <b>Rearfoot Posting:</b> Crepe Firm @ 0°/0°  <b>Additional:</b> "Ski Loop" for easy removal  <b>Covers:</b> Full Length 1/16" Neoprene Top, Ultrasuede Bottom</p>	<p><b>Carbo Dress</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Shallow  <b>Shell Width:</b> Narrow  <b>Cast Fill:</b> Normal  <b>Shell:</b> Carboplast II 2.0mm "Semi-Rigid"  <b>Rearfoot Posting:</b> None  <b>Additional:</b> Heel Hole  <b>Covers:</b> Sulcus Length PPT Extension, Black Vinyl Top, Scrim bottom</p>	<p><b>Lateral Ankle Instability</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal + 2° Lateral Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Crepe Firm (Lateral Only) @ 0°/0°, No Lateral Bevel  <b>Additional:</b> Reverse Morton's Ext. @ 3° Lat.  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Lateral Column Overload (also, P.Tendonitis)</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal + 2° Lateral Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> EVA (Medium) Lateral Arch Fill Reverse Morton's Extension  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Soft Step</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 3/32" Polypropylene  <b>Rearfoot Posting:</b> None  <b>Additional:</b> EVA (Medium) Arch Fill  <b>Covers:</b> Full Length 1/16" PPT Cushion, 1/16" Neoprene Top, Ultrasuede Bottom</p>	<p><b>Cork &amp; Leather</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Normal  <b>Shell:</b> Thermocork  <b>Rearfoot Posting:</b> Integrated into Shell  <b>Additional:</b> Integrated Arch Fill  <b>Covers:</b> Full Length 1/16" PPT Cushion, Tan Leather Top, Multicork Bottom</p>	<p><b>Metatarsalgia</b>  <b>Heel Bisection:</b> Inverted 2°  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight, No Distal Edge Bevel  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> 3mm Metatarsal Raise  <b>Covers:</b> Full Length 1/8" Poron Extension, 1/8" Puff EVA Top, Scrim Bottom</p>	<p><b>Neuroma</b>  <b>Heel Bisection:</b> Inverted 2°  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> None  <b>Additional:</b> 3mm Metatarsal Pad  <b>Covers:</b> Full Length 1/8" Poron Forefoot Ext. 1/8" Puff EVA Top, Scrim Bottom</p>
<p><b>Poly Accommodative</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Shallow  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 3/32" Polypropylene  <b>Rearfoot Posting:</b> None  <b>Additional:</b> EVA (Medium) Arch Fill  <b>Covers:</b> Full Length 1/16" PPT Cushion, Black Vinyl Top, HR EVA Bottom</p>	<p><b>AliPlast Accommodative</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Shallow  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> AliPlast XPE Polyethylene Foam  <b>Rearfoot Posting:</b> Integrated  <b>Additional:</b> EVA (Medium) Arch Fill  <b>Covers:</b> Full Length "6/6" Blue BiLam (PPT + Blue EVA) Top, HR EVA Bottom</p>	<p><b>Pes Cavus with Rigid Forefoot</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0° No Lateral Bevel  <b>Additional:</b> 3mm Heel Lift, Reverse Morton's Ext. @ 3° Lat., 3mm Met. Pad  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Plantar Fasciitis due to Everted Rearfoot</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep + 3° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> None  <b>Additional:</b> None  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Foot Forms Cork</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 1.8mm 55 Duro Milled Cork/EVA Base  <b>Rearfoot Posting:</b> Integrated  <b>Additional:</b> Integrated Arch Fill  <b>Covers:</b> Full Length 1/8" Puff EVA Top, Integrated Bottom</p>	<p><b>Foot Forms Blue</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Normal  <b>Cast Fill:</b> Normal  <b>Shell:</b> 2.2mm 45 Duro Milled Blue EVA Base  <b>Rearfoot Posting:</b> Integrated  <b>Additional:</b> Integrated Arch Fill  <b>Covers:</b> Full Length 1/16" Perforated Puff Top, Integrated Bottom</p>	<p><b>Plantar Fasciitis due to Forefoot Valgus</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Normal  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> None  <b>Additional:</b> Reverse Morton's Extension  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Sesamoiditis</b>  <b>Heel Bisection:</b> Inverted 3°  <b>Heel Cup:</b> Normal + 2° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight, No Distal Edge Bevel  <b>Rearfoot Posting:</b> None  <b>Additional:</b> Reverse Morton's Extension  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Poly Hybrid Diabetic</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Normal  <b>Shell:</b> Aliplast XPE + 3/32" Polypropylene  <b>Rearfoot Posting:</b> None  <b>Additional:</b> None  <b>Covers:</b> Full Length "8/8" Pink BiLam (PPT + Plastazote) Top, HR EVA Bottom</p>	<p><b>White EVA DMII Insole</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> 35 Duro Milled White EVA Base  <b>Rearfoot Posting:</b> Integrated  <b>Additional:</b> Integrated Arch Fill  <b>Covers:</b> Full Length "6/6" Pink BiLam (PPT + Plastazote) Top, Integrated Bottom</p>	<p><b>Sinus Tarsi Syndrome</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep + 2° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> Reverse Morton's Extension  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>	<p><b>Tarsal Tunnel Syndrome</b>  <b>Heel Bisection:</b> Inverted 2°  <b>Heel Cup:</b> Deep + 3° Medial Heel Skive  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Semi Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> 4mm Heel Lift  <b>Covers:</b> Full Length 1/8" Puff EVA Top</p>
<p><b>Cork EVA DMII Insole</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide  <b>Cast Fill:</b> Light  <b>Shell:</b> 55 Duro Milled White EVA Base  <b>Rearfoot Posting:</b> Integrated  <b>Additional:</b> Integrated Arch Fill  <b>Covers:</b> Full Length "8/8" Pink BiLam (PPT + Plastazote) Top, Integrated Bottom</p>	<p><b>Whitman Roberts (also, Pediatric Flatfoot)</b>  <b>Heel Bisection:</b> Inverted 2°  <b>Heel Cup:</b> Deep + 2° Medial Heel Skive  <b>Shell Width:</b> Wide + Medial Flange + Lat Clip  <b>Cast Fill:</b> Light  <b>Shell:</b> Polypropylene Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> None  <b>Covers:</b> None</p>	<p><b>In-toeing Gait Plate</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide + Medial Flange + Lat Clip  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> Shell extension @ 4th and 5th Met  <b>Covers:</b> None</p>	<p><b>Out-toeing Gait Plate</b>  <b>Heel Bisection:</b> Perpendicular  <b>Heel Cup:</b> Deep  <b>Shell Width:</b> Wide + Medial Flange + Lat Clip  <b>Cast Fill:</b> Normal  <b>Shell:</b> Polypropylene Rigid by Weight  <b>Rearfoot Posting:</b> Polypropylene @ 0°/0°  <b>Additional:</b> Shell extension @ 1st Met  <b>Covers:</b> None</p>